

COVERALL

FOR HEALTHCARE PROFESSIONALS

Functional and versatile PVC goggles that fit over prescription glasses, COVERALL goggles combine ultimate protection and comfort to help reduce workplace accidents. Equipped with an **anti-scratch and anti-fog coating** on both sides of the lenses, COVERALL ensures long-lasting comfort, performance and reliability. Suitable for healthcare industry.



1686101 • Clear Indirect Vents



91 g




- + ECONOMIC MODEL**
- + ADJUSTABLE NYLON STRAP**
- + FITS OVER PRESCRIPTION GLASSES**
- + VENTILATED FRAME**
- + MEDIUM IMPACT AND CHEMICAL SPLASH PROTECTION APPROVED**

bolle
SAFETY

COVERALL

FOR HEALTHCARE PROFESSIONALS

MODEL	VERSIONS	REFERENCES	LENS MARKING	FRAME MARKING	COATINGS
COVERALL	 Clear Indirect Vented	1686101	CIO	AS/NZS 1337.1:2010	Anti-scratch/Anti-fog

LENS MARKING

- C.** The letter 'C' signifies that the product has been tested and approved for use against splashes and is appropriate for chemical handling.
- I.** The letter 'I' signifies 'Medium Impact' approval.
- O.** The letter 'O' signifies that the product has been approved for the use both outdoors and indoors, and the terminology used by Australian standards is 'outdoor un-tinted'. This marking appears on all clear, amber and contrast lenses.

Ocular lens category:

- O.** Range of luminous transmittance 80–100% (Clear).

LENSES

- Anti-fog / anti-scratch coating on both sides of Clear Ventilated model lens
- 99.9% UV 385 - Clear

FRAME MARKING

AS/NZS 1337.1:2010 : Tested and approved to AS/NZS 1337.1:2010 for medium impact protection. Resists a 6mm ball at 45 m/s. Meets the requirements of splash approval when used with the supplied head strap correctly adjusted.

CLEANING AND STORAGE

CLEANING: The lenses should be cleaned regularly. Bollé Safety recommends only using the B-clean lens cleaning system.

MAINTENANCE: Pitted, scratched or damaged lenses must be replaced by replacing the complete product. If the frame is damaged also replace the complete product. After each use it is recommended to keep the spectacles or goggles in a microfiber pouch or rigid case.

STORAGE: All products must be stored in a dry and clean environment.

Always read and follow the instructions on the label.

CHARACTERISTICS	
LENSES	PC - 2,2 mm - Curve 4
FRAME	PVC
TEMPLES	Non applicable
STRAP	Nylon
FOAM	No
SPARE LENSES	No



Non-contractual pictures
26/05/2021

ASIA/PACIFIC HEADQUARTERS:

Bollé Safety AU Pty Limited
32-40 Fairchild Street
Heatherton VIC 3202
T: 1300 138 098
E: sales@bollesafety.com.au

bollesafety.com.au

NEW ZEALAND:

T.: 0800 2655 369
E: sales@bollesafety.com.au

bolle
SAFETY